



PerfectDry Lux® UV-C

UV-C disinfection and quick drying of hearing systems.

Performance, Quality, Design

PerfectDry Lux® has been designed for an optimal fast drying with a real and effective disinfection of hearing systems.

The quality, the design and the optimal size of PerfectDry Lux® make it a perfect setting for hearing systems.

Conditioning: 1 box with 1 PerfectDry Lux, 1 USB cable, 1 x 5V adapter and user instructions



- 30 minute drying time
- 360°C UV-C disinfection
- Forced-air fan drying system
- Quality and sturdiness
- Optimized ergonomics
- Low energy consumption
- Compact case and design
(L. 90 mm/3.54 in)
- USB or power supply (UL)

